# 11800

## 91-93 HONDA ACCORD WAGON

### 11/13/2020


GROSS LOAD CAPACITY WHEN USED AS A WEIGHT CARRYING HITCH: 2,500 LBS. TRAILER WEIGHT & 200 LBS. TONGUE WEIGHT.

\*\*\*DO NOT EXCEED VEHICLE MANUFACTURER'S RECOMMENDED TOWING CAPACITY.\*\*\*

WARNING: ALL NON-TRAILER LOADS APPLIED TO THIS PRODUCT MUST BE SUPPORTED BY AUXILIARY STABILIZING STRAPS.

#### \*\* FAILURE TO PROPERLY SUPPORT NON-TRAILER LOADS WILL VOID PRODUCT WARRANTY\*\*

HAVING INSTALLATION QUESTIONS? CALL TECHNICAL SUPPORT AT 877-287-8634



### **INSTALLATION STEPS**

- 1. Locate the left and right frame rails under the rear of the car. Remove the tie down brackets (two 10mm screws each) and the plastic shield at the rear corner of the rails. Use phillips screw driver to pry plastic expansion plug out. Also remove the screw fastening the muffler shield at the bottom of the right rail. Hammer the edge of the heat shield flat against the frame rail. The heat shield will be sandwiched between the hitch and frame. Return all parts to the car's owner should the hitch ever be removed.
- 2. Lift the hitch into position on the frame rails. Fasten the hitch to the frame rails as shown. With the hitch bolted into position; use the hitch as a template to drill holes for the rear most fasteners. Remove the hitch from the car.
- 3. Using an 1 1/4" hole saw, make one clearance hole in the bottom surface of each frame rail located as shown in the diagram so it will be covered when the hitch is installed. These holes provide access to fishwire carriage bolts and backing plates into the frame rails with the threaded end extending from holes.
- 4. Reinstall the hitch on the car being careful to not push the carriage bolts out. Complete the installation using the balance of the fasteners called out in the diagram. Be careful to use washers as shown.
- 5. Torque all 10mm fasteners to 48 lb-ft and all 7/16" fasteners to 59 lb-ft.

PERIODICALLY CHECK THIS RECEIVER HITCH TO ENSURE THAT ALL FASTENERS ARE TIGHT AND THAT ALL STRUCTURAL COMPONENTS ARE SOUND.

Curt Manufacturing Inc., warrants this product to be free of defects in material and/or workmanship at the time of retail purchase by the original purchaser. If the product is found to be defective, Curt Manufacturing Inc., may repair or replace the product, at their option, when the product is returned, prepaid, with proof of purchase. Alteration to, misuse of, or improper installation of this product voids the warranty. Curt Manufacturing Inc.'s liability is limited to repair or replacement of products found to be defective, and specifically excludes liability for incidental or consequential loss or damage.